Electrical Connector Backshell - Page 1 of 2



View Online at https://aerobasegroup.com/nsn/5935-01-145-2194

Thread Class: 2b Thread Direction: Right-hand Seal Material: Rubber Overall Width: 1.688 inches Body Angle In Deg: 45.0 Cable Opening Diameter: Between 0.562 inches and 0.937 inches Distance From Centerline To Connector End: 1.999 inches Distance From Centerline To Cable End: 3.062 inches Cable Opening Quantity: 1 Seal Type:
Thread Direction: Right-hand Seal Material: Rubber Overall Width: 1.688 inches Body Angle In Deg: 45.0 Cable Opening Diameter: Between 0.562 inches and 0.937 inches Distance From Centerline To Connector End: 1.999 inches Distance From Centerline To Cable End: 3.062 inches Cable Opening Quantity: 1
Right-hand Seal Material: Rubber Overall Width: 1.688 inches Body Angle In Deg: 45.0 Cable Opening Diameter: Between 0.562 inches and 0.937 inches Distance From Centerline To Connector End: 1.999 inches Distance From Centerline To Cable End: 3.062 inches Cable Opening Quantity: 1
Seal Material: Rubber Overall Width: 1.688 inches Body Angle In Deg: 45.0 Cable Opening Diameter: Between 0.562 inches and 0.937 inches Distance From Centerline To Connector End: 1.999 inches Distance From Centerline To Cable End: 3.062 inches Cable Opening Quantity: 1
Rubber Overall Width: 1.688 inches Body Angle In Deg: 45.0 Cable Opening Diameter: Between 0.562 inches and 0.937 inches Distance From Centerline To Connector End: 1.999 inches Distance From Centerline To Cable End: 3.062 inches Cable Opening Quantity: 1
Overall Width: 1.688 inches Body Angle In Deg: 45.0 Cable Opening Diameter: Between 0.562 inches and 0.937 inches Distance From Centerline To Connector End: 1.999 inches Distance From Centerline To Cable End: 3.062 inches Cable Opening Quantity: 1
 1.688 inches Body Angle In Deg: 45.0 Cable Opening Diameter: Between 0.562 inches and 0.937 inches Distance From Centerline To Connector End: 1.999 inches Distance From Centerline To Cable End: 3.062 inches Cable Opening Quantity: 1
Body Angle In Deg: 45.0 Cable Opening Diameter: Between 0.562 inches and 0.937 inches Distance From Centerline To Connector End: 1.999 inches Distance From Centerline To Cable End: 3.062 inches Cable Opening Quantity: 1
45.0 Cable Opening Diameter: Between 0.562 inches and 0.937 inches Distance From Centerline To Connector End: 1.999 inches Distance From Centerline To Cable End: 3.062 inches Cable Opening Quantity: 1
Cable Opening Diameter: Between 0.562 inches and 0.937 inches Distance From Centerline To Connector End: 1.999 inches Distance From Centerline To Cable End: 3.062 inches Cable Opening Quantity: 1
Between 0.562 inches and 0.937 inches Distance From Centerline To Connector End: 1.999 inches Distance From Centerline To Cable End: 3.062 inches Cable Opening Quantity: 1
Distance From Centerline To Connector End: 1.999 inches Distance From Centerline To Cable End: 3.062 inches Cable Opening Quantity: 1
 1.999 inches Distance From Centerline To Cable End: 3.062 inches Cable Opening Quantity: 1
Distance From Centerline To Cable End: 3.062 inches Cable Opening Quantity: 1
3.062 inches Cable Opening Quantity: 1
Cable Opening Quantity:
1
Seal Type:
Preformed packing
Size Designation:
20
Mounting Facility Type And Quantity:
1 threaded coupling
Thready Qty Per Inch (tpi):
18
Thread Size:
1.125 inches
Material:
Aluminum alloy
Surface Treatment:
Cadmium and chromate
Style Designator:
Angle type w/clamp
Surface Treatment:
Cadmium and chromate
Thread Series Designator:
Unef
Shelf Life:
N/a
Unit Of Measure:

Electrical Connector Backshell - Page 2 of 2



Demilitarization:

No

Fiig:

A10100