

View Online at <https://aerobasegroup.com/nsn/6525-01-485-9922>

Product Name:

Processor dental x-ray film 115v 60hz water recirculation system

Special Features:

Heater pad/thermistor system to assure chemistry temp; auto replenishes chemistry proportional to film load; control panel w/light touch keypads, indicator lights, led temp display; endo speed: 2.5 min for quick look; normal speed: 5.5 min for archival quality dental films; 3 hose drain system for chemistry and wash water capture; handles all dental film sizes: panoramic, cephalometric, tmj, occlusal and periapicals; energy saving auto on/off; separate dedicated 15 amp line is recommended; stationary design type; manual operation method; 115.0 voltage in volts; 8.0 current rating in amps; 60.0 hertz frequency

Supplementary Features:

With built in water recirculation system; includes leveling base; bottle spray 2000, 4 air techniques cleaning films, a/t 2000 xr video, 1 case chemistry 40270, 1 bottle of starter 40280; see nsn 6525-01-471-7140 for a/t 2000 xr automatic film processor without built in recirculation system

Shelf Life:

N/a

Unit Of Measure:

--

Demilitarization:

No