

View Online at <https://aerobasegroup.com/nsn/6525-01-512-1960>

Current Type:

Ac

Frequency Rating:

60.0 hertz

Specific Use:

Film processing machine

Loading Characteristic:

Daylight

Usage Design:

Film

Installation Design:

Portable

Temperature Controlled Feature:

Included

Loading Type:

Magazine

Product Name:

Model a/t 2000 x-ray film processor

Voltage In Volts:

115.0

Phase:

Single

Special Features:

8 amps; three prong plug required; 2.5 minute endo quick look film processing; 5.5 minute archival film processing; water flow .5 gpm; requires 80 psi maximum water pressure with 30psi min; water source must have manual shut off near processor; adapters to connect .5 inch mpt or .75 inch male garden hose fitting; supplied tubing at rear of processor is 6 feet long; vacuum breaker not required; 1 inch air gap between water supply inlet and top of tank; water temp 55 degrees f to 80 degrees f; mixing valve not required if water temp is in range; 1.5 inch pvc standpipe connected to a 1.5 inch pvc trap; do not drain into copper or brass

Shelf Life:

N/a

Unit Of Measure:

--

Demilitarization:

No

Fig:

T150-c